

1904 Industrial Way, Caldwell, ID 83605 208-454-2597

Model Q5715-P 1 Micron Lead Reduction Block w/Scale Inhibitor

IMPORTANT NOTICE

Read this Performance Data Sheet and compare the capabilities of this unit with your actual water treatment needs. It is recommended that, before purchasing a water filter unit, you have your water supply tested to determine your actual water treatment needs.

| Standard 42 Aesthetic Effects/Standard 53 Health Effects | | | | | | |
|--|------------------|----------------------|------------------|------------------|---------------------------|---------------------------|
| Parameter | US EPA MCL | Influent Challenge | Effluent Average | Effluent Maximum | Percent Reduction Average | Percent Reduction Minimum |
| Chlorine | - | 2.0 mg/L | 0.03 mg/L | 0.06 mg/L | 98.5 | 97 |
| Cyst | 99.95% Reduction | 111,750 Particles/ml | 1 particle/ml | 2 particles/ml | 99.99% | 99.99 |
| Lead pH 8.5 | 15 ug/L | 135 ug/L | 5.5 ug/L | 13 ug/L | 95.9% | 90 |
| Lead pH 6.5 | 15 ug/L | 149 ppb | 1 ug/L | 1 ug/L | 99% | 99 |

¹Tested using flow rate = 0.5 gpm; pressure = 60 psig; pH = 8.5 and 6.5; temp. = 20° ± 2.5° C

Operating Specifications

Capacity: 2,000 Gallons Lead reduction/6 Months Scale Inhibition
Flow Rate: 0.50 GPM (1.9 LPM)
Maximum Pressure: 125 PSIG
Temperature: 35-100° F (2-38° C)

General Installation/Operation/Maintenance Requirements

- Note flow direction of filter.
- Flush new cartridge with 5 gallons of water through filter at the rated service flow before use and check for leaks. If leaks occur, check tightness of tubing and fittings. If leaks persist, discontinue use and call your supporting dealer.
- Replace cartridge when rated capacity is reached, or when flow becomes too slow.
- Install in compliance with state and local laws and regulations.

Special Notices

- Systems certified for cyst reduction may be used on disinfected waters that may contain filterable cysts.
- "Do not use with water that is micro biologically unsafe or of unknown quality without adequate disinfection before or after the system.

Warranty Information

Omnipure Filter Company (Omnipure) warrants that the products delivered will be free from any defects in workmanship or materials. Further, the warranty provided herein applies, only when used within the products specifications and service life, from the date of installation, beyond which time or use Omnipure is absolved of any and all liability for any use of the product. In the event of defect or non-conformity, buyer shall promptly notify Omnipure in writing, supplying proof of purchase dates, installation dates, and will protect and retain the products for investigation, or Omnipure is absolved of any and all liability for any use of the product. There are no other warranties, either merchantability or fitness, either expressed or implied.